

(direct drive, 450nm-2630nm)



DATASHEET

Return to the Webpage



Features

- High Repeatability
- Low Power
- Small

The VOAD series variable optical attenuators feature direct drive by a function generator having bandwidth up to 1.5KHz, provide attenuation up to >30 dB. It is a convenient tool for laboratory use. Driving voltages of 0 to 10 V control optical transmission without polarity, which decreases with applied voltage with modulation up to 1.5 kHz. Most voltage sources, including power supplies, function generators, and digital-to-analog converters (DACs), can be used to control these electronic VOAs. The VOA is optically bidirectional. The VOAD is constructed using an electrostatic rotating mirror hermetically sealed with nitrogen, featuring high repeatability, low power consumption, and low cost. However, the device can be damaged by applied a voltage over 15V. The device's electrical character is capacitive without polarity.

Specifications

Para	Min	Typical	Max	Unit		
Operation	Single Mode	Single Mode 450		2300		
Wavelength	Multimode	810-890		1260-1600	nm	
Insertion Loss [1], [2]	0.5		5	dB		
PDL (SM)			0.3	dB		
Repeatability (0-30, @		0.1	0.2	dB		
Wavelength Depende			0.63	dB		
Extinction Ratio	PM fiber	16		30 ^[3]	dB	
Repeatability	Uncompensated		0.3	0.5	dB	
(@10dB, 0-60 °C)	Compensated		0.1	0.2		
Return Loss	SM, PM	50			dB	
	MM	35				
Attenuation	SM, PM	40			dB	
	MM	30				
Driving Voltage	SM, PM	0	5	7	٧	
	MM	0	5	9		
Response Time		0.3	1	ms		
Repetition Rate		50	1500	Hz		
Durability		10 ¹²		cycle		
Power Consumption (0.2	mW		
ESD			500	V		
Operating Temperatu	-10		70	°C		
Storage Temperature	-40		85	°C		
Optical Power Handlin		300	400	mW		

Notes:

- [1]. The loss is related to the fiber core size and the connector mating. <1dB for 1230-1630nm. Above this band the fiber has high loss. Below this band, the loss is inversely proportional to fiber core size and connector mating (if center off then higher loss).
- [2]. Multimode IL measured @ Light Source CPR < 14dB
- [3]. 30dB PER is available with special order
- [4]. The power handling is inversely proportional to fiber core size. 300mW for 1230-1630nm SM.

Legal notices: All product information is believed to be accurate and is subject to change without notice. Information contained herein shall legally bind Agiltron only if it is specifically incorporated into the terms and conditions of a sales agreement. Some specific combinations of options may not be available. The user assumes all risks and liability whatsoever in connection with the use of a product or its application.

Rev 02/26/25

© Photonwares Corporation

P +1 781-935-1200

E sales@photonwares.com

w www.agiltron.com




(direct drive, 450nm-2630nm)



DATASHEET

Mechanical Dimensions (mm)



dimensions tolerance to be +/-0.2mm

Electrical Driving Requirements

- 1) Capacitive load device, no polarity.
- 2) The maximum rating voltage is 10V

^{*}Product dimensions may change without notice. This is sometimes required for non-standard specifications.



(direct drive, 450nm-2630nm)



DATASHEET

Operation Manual

- Unpack the unit carefully
- Connect light source and detector. Either of the unit's fiber leads can be used as the input or output
- Use a BNC cable to connect a power supply or other voltage source to the unit, and then apply 0 to 8 V to control the attenuation. Please note that minimum attenuation and polarization-maintaining performance are highly dependent on connector alignment. Best performance is achieved when the optical connection is made by fusion splicing to the VOA's fiber leads, which requires removing the connectors.
- If connect to a function generator, making sure the setting is one polarity not + driving.

Ordering Information

	Т		7	1	1		3	1	
Prefix	Non-Power State	Wavelength	Package	Туре	Compensation	Fiber Type	Fiber Cover	Fiber Length	Connector
VOAD-	Transparent = T	1260~1650nm = 5 460nm = 3 630nm = 6 780nm = 7 850nm = 8 1060nm = 1 2000nm = 2	BNC = 7	Standard = 1 Special = 0	Non = 1	SMF-28 = 5 PM1550 = B MM 62.5/125 = 6 SM450 = 4 SM600 = A 780HP = 7 Hi1060 = 1 PM460 = C PM630 = D PM780 = E PM980 = F	0.9mm tube = 3	0.5-1m = 1	FC/APC = 3

Application Notes

Fiber Core Alignment

Note that the minimum attenuation for these devices depends on excellent core-to-core alignment when the connectors are mated. This is crucial for shorter wavelengths with smaller fiber core diameters that can increase the loss of many decibels above the specification if they are not perfectly aligned. Different vendors' connectors may not mate well with each other, especially for angled APC.

Fiber Cleanliness

Fibers with smaller core diameters ($<5 \mu m$) must be kept extremely clean, contamination at fiber-fiber interfaces, combined with the high optical power density, can lead to significant optical damage. This type of damage usually requires re-polishing or replacement of the connector.

Maximum Optical Input Power


Due to their small fiber core diameters for short wavelength and high photon energies, the damage thresholds for device is substantially reduced than the common 1550nm fiber. To avoid damage to the exposed fiber end faces and internal components, the optical input power should never exceed 20 mW for wavelengths shorter 650nm. We produce a special version to increase the how handling by expanding the core side at the fiber ends.



(direct drive, 450nm-2630nm)



Typical Frequency Response for SM28 Fiber Channel 1: VOA signal; Channel 2: Drive signal (0 to 5V)







(direct drive, 450nm-2630nm)



Typical Attenuation vs. Voltage at 25°C, 55°C, 70°C 1550nm SM



Typical Insertion Loss vs Wavelength (1240-1630nm)











(direct drive, 450nm-2630nm)



Wavelength Dependence 10 dB, 1550nm SM



Wavelength Dependence 0.5 dB, 1550nm SM








(direct drive, 450nm-2630nm)



Typical Wavelength Dependence @20dB Attenuation










(direct drive, 450nm-2630nm)



DATASHEET

Typical Voltage Variable Attenuation Repeatability over 5days (5 colors) 1550nm SM



Optical Power Handling vs Wavelength for Standard SM Fibers

